



## Retaining ring for bores - normal type DIN 472 Stainless spring steel 1.4122/1.4021 29MM

Article number	51437.029.001
Brand	-
UBB	950357356795
UNSPSC	31163202
EAN	8715492290236
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	29 mm
For nom. size	29mm
Material	Stainless spring steel
Material technical	1.4122/1.4021
Nom. size bore d1	29

#### Info

Other types of stainless steel than specified (but with equal properties) may be supplied at the discretion of the manufacturer. Avoid contact with chloride containing (cleaning-) liquids in order to reduce the risk of chloride induced stress corrosion cracking. d4 is the minimum required installation space. During assembly it is essential to not over-compress the rings, a maximum compression of  $0,99 \times d1$  is

### Standards

NF	E22-165
BS	3673-4
DIN	472

recommended. For proper installation use pliers with spread limiter or assemble with the aid of a cone.

## Technical Specification

Groove d2	30.4
Groove m (H13)	1.3
Groove n (min.)	2.1
Ring d3	31.1
Ring d4	19.6
Ring s	1.2
Ring b $\approx$	3

## Technical Drawing

