



## Retaining ring for bores - normal type DIN 472 Stainless spring steel 1.4122/1.4021 60MM

Article number	51437.060.001
Brand	-
UBB	950357149711
UNSPSC	31163202
EAN	8715492290427
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	60 mm
For nom. size	60mm
Material	Stainless spring steel
Material technical	1.4122/1.4021
Nom. size bore d1	60

#### Info

Other types of stainless steel than specified (but with equal properties) may be supplied at the discretion of the manufacturer. Avoid contact with chloride containing (cleaning-) liquids in order to reduce the risk of chloride induced stress corrosion cracking. d4 is the minimum required installation space. During assembly it is essential to not over-compress the rings, a maximum compression of  $0,99 \times d1$  is

### Standards

NF	E22-165
BS	3673-4
DIN	472

recommended. For proper installation use pliers with spread limiter or assemble with the aid of a cone.

## Technical Specification

Groove d2	63
Groove m (H13)	2.15
Groove n (min.)	4.5
Ring d3	64.2
Ring d4	44.7
Ring s	2
Ring b $\approx$	5.4

## Technical Drawing

