

Hexagon head bolt DIN 931 Stainless steel A4 80 M10X90

Article number	53510.100.090
Brand	-
UBB	950351832197
UNSPSC	31161620
EAN	8715492318046
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	90 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

DIN	931
NF	E25-112
ASME	B18.2.3.1M
ISO	4014
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	90
P	1.5
s	17

Technical Drawing

