

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M36X170

Article number	55000.360.170
Brand	-
UBB	951351781764
UNSPSC	31161620
EAN	8715492322364
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M36
Length	170 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ASME	B18.2.3.1M
NF	E25-112
ISO	4014
DIN	931
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	84
b (min.): L200mm	97
b (min.): L≤125mm	78
d-D	M36
k	22.5
L (mm)	170
P	4
s	55

Technical Drawing

