



Hexagon socket head cap screw DIN 912 Stainless steel A4 70 M12X60

Article number	55050.120.060
Brand	-
UBB	950351879883
UNSPSC	31161605
EAN	8715492328762
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M12
Length	60 mm
Class	70
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

ASME	B18.3.1M
NF	E25-125
DIN	912
BS	4168-1
NEN	1241
ISO	4762

Technical Specification

b	36
d-D	M12
dk (max.)	18
Full thread if L ≤	50
k (max.)	12
L (mm)	60
P	1.75
s	10

Technical Drawing

