



Slotted countersunk head screw DIN 963 A Stainless steel A4 M5X40

Article number	55110.050.040
Brand	-
UBB	950353293257
UNSPSC	31161504
EAN	8715492333933
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M5
Length	40 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NF	≈E25-123
NEN	≈2370
BS	≈4183
DIN	963
ISO	≈2009
ASME	≈B18.6.7M

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if $L \leq$	30
k (max.)	2.5
L (mm)	40
n	1.2
P	0.8
t (min.)	1

Technical Drawing

