



Threaded rod Permaglas
Glass Fibre Reinforced
Plastic ME 771 M8X950

Article number	56050.080.950
Brand	-
UBB	951353175270
UNSPSC	31161618
EAN	8715492859990
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M8
Length	950 mm
Color	Red
Material	Glass-fibre reinforced plastic
Material technical	Permaglas ME 771
Thread direction	Right
Thread	Metric thread

Info	Special features PERMAGLAS ME 771:Glass-fiber reinforced epoxy Temperature resistant – 270°C up to +155°C Light weight (density 1,9-2,0 g/cm³) Corrosion resistant, highly UV- and weather resistant Resistant to aggressive chemicals and gases Provides electrical and thermal insulation Non-magnetic Better mechanical
------	---

Standards

properties than e.g.
Polyamide

FABORY

Technical Specification

d-D	M8
L (mm)	950
P	1.25

Technical Drawing

