



DIN ≈912 Plastic Polyamide (nylon) 6.6 M8X25

Article number	56120.080.025
Brand	-
UBB	955351287300
UNSPSC	31161605
EAN	8715493538276
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M8
Length	25 mm
Class	6.6
Color	White
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Plastic
Material technical	Polyamide (nylon)
Thread direction	Right
Thread	Metric thread

Standards

ASME	≈B18.3.1M
NF	≈E25-125
ISO	≈4762
BS	≈4168-1
DIN	≈912
NEN	≈1241

Technical Specification

d-D	M8
dk (max.)	13
k (max.)	8
L (mm)	25
P	1.25
s	6

Technical Drawing

