



KIPP Cam levers, external thread Black Cast aluminium EN AC-46200/stainless steel 1.4305 M3X12,0X15

Article number	58006.030.015
Brand	-
UBB	500689424371
UNSPSC	31162807
EAN	4059245210169
PKG. of 1	Full Box Only

Technical Parameters

Color	Black
D1_MM	12mm
Material	Cast aluminium/ stainless steel
Material technical	EN AC-46200/1.4305
Thread	Metric thread

Info

Material: Handles cast aluminium EN AC-46200. Thrust washer plastic PA 66 GF 35-X fibreglass reinforced. Hinge pins stainless steel 1.4305. Studs and washer steel grade 5.8. Version: Handles fine structured powder-coated, black. Thrust washer, black. Hinge pin, bright. Studs and washer zinc plated, blue passivated steel. Note: Adjustable cam levers are used if the position of the lever

Standards

FABORY

relative to the axis of tension only permits one specific position (interference circle). The exact position of the lever is adjusted using a screwdriver on the fine thread setscrew. Plastics are subject to creeping under load (retardation).Drawing reference: 1) setscrew for fine adjustment of lever.adjustable

Technical Specification

A	36.2
A1	41.7
B	14.4
B1	11.5
Hand force FH (N)	90
D	3
D1	12
D2	6
F	1
H	9
H1	13
L	15
S	1

Technical Drawing

