



FISCHER Wall plugs Duopower Plastic Nylon 6X30

Article number	63280.060.030
Brand	-
UBB	500654176725
UNSPSC	31162103
EAN	4048962239836
PKG. of 1	Full Box Only

Technical Parameters

Diameter	6 mm
Length	30 mm
Color	Grey/Red
Material	Plastic
Material technical	Nylon
Type no.	DUOPOWER

Standards

Technical Specification

Brick Mz12	0.4
Cellular concrete PB2, PP2 (G2)	0.06
Cellular concrete PB4, PP4 (G4)	0.3
Concrete C20/25	0.8
D (mm)	6
Drill depth (min.)	40
Drill ø	6
Hollow sandlime brick KSL12	0.5
L (mm)	30
Material thickness (min.)	12.5
Plasterboard ≥ 2x12,5mm	0.12

Plasterboard 0.12
12,5mm

Sandlime brick KS12 0.8

Ventilation stone 0.15
Hlz12

Wood or chipboard 5
screws