



Brady Energy source tag GL-2-75X38MM-PP 25PC

Article number	7D697741
Brand	-
UBB	500671989571
UNSPSC	46180000
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Width (mm)	75
Max. service temp. °C	120 °C
Min. service temp. °C	-40 °C
Content (pcs)	25
Number of holes	1
Height (mm)	38
Length (L) (mm)	75
Thickness	1.55
Weight (g)	1

Standards