



**Bosch Cordless Rotary
hammer L-Boxx GBH 18 V-26
F**

Article number	8W299606
Brand	-
UBB	500700213605
UNSPSC	27112700
EAN	3165140807944
PKG. of 1	Full Box Only

Technical Parameters

Nominal voltage	18
Length	378
Drill diameter in concrete	26
Max. single-blow energy	2.6
Tool insertion	SDS-plus socket
Drill diameter in wood	30
Max. number of strokes	4350
Idle rotational speed	890
With battery charger	No
Model	Click&Go
Safety	GBH 18 V-26 F
Type	BH_NF_inh_02_EN

Standards