



Bosch Drill GBM16-2RE-1050W

Article number	B4300.000.050
Brand	-
UBB	500505900042
UNSPSC	23101502
EAN	3165140147644
PKG. of 1	Full Box Only

Technical Parameters

Voltage	230
Nominal power consumption	1050
Machine weight	3.7
Drill chuck span	16
Drill diameter steel 2nd gear	8
Drill diameter steel 1st gear	16
Drill diameter wood 2nd gear	20
Drill diameter wood 1st gear	40
Max. torque	50
Tool insertion	B16
Max. on-load speed 1st gear	400
Max. on-load speed 2nd gear	950
Type of drill holder	Key-type
Idle rotational speed 1st gear	600
Idle rotational speed 2nd gear	1450

Standards