



Bosch Jigsaw GST150CE

Article number	B4500.000.050
Brand	-
UBB	500571224889
UNSPSC	27111508
EAN	3165140463720
PKG. of 1	Full Box Only

Technical Parameters

Stroke	26
Voltage	230
Nominal power consumption	780
Machine weight	2.6
Cutting depth in wood	150
No-load stroke rate	500
Max. material thickness in aluminium 250 N/mm ²	20
Max. material thickness in steel 400 N/mm ²	10

Standards