

Pullers 30-1 clamp depth 100 mm clamping width 90 mm 6 t KUKKO

Article number	E9030.030.001
Brand	-
UBB	240127013714
UNSPSC	27111712
EAN	4021176013393
PKG. of 1	Full Box Only

Technical Parameters

Model	Other
Wrench width	17
Max. tensile force	6
Number of hooks	3
Reversible arms	Yes
Clamping reach	100
Depth of hooked foot	100
Clamping spread (internal pulling)	70 - 70
Max. clamping spread (external pulling)	90

Standards