

## Pullers 30-10 clamp depth 100 mm clamping width 130 mm 6 t KUKKO

|                |               |
|----------------|---------------|
| Article number | E9030.030.010 |
| Brand          | -             |
| UBB            | 240127014050  |
| UNSPSC         | 27111712      |
| EAN            | 4021176013621 |
| PKG. of 1      | Full Box Only |

### Technical Parameters

|                                               |         |
|-----------------------------------------------|---------|
| Model                                         | Other   |
| Wrench width                                  | 17      |
| Max. tensile force                            | 6       |
| Number of hooks                               | 3       |
| Reversible arms                               | Yes     |
| Clamping reach                                | 100     |
| Depth of hooked foot                          | 100     |
| Clamping spread<br>(internal pulling)         | 70 - 70 |
| Max. clamping<br>spread (external<br>pulling) | 120     |

### Standards