



Pullers 44-3 clamp depth 160 mm clamping width 160 mm 6 t KUKKO

Article number	E9044.044.003
Brand	-
UBB	240127020313
UNSPSC	27111712
EAN	4021176016288
PKG. of 1	Full Box Only

Technical Parameters

Model	Other
Max. tensile force	6
Number of hooks	2
Clamping reach	160
Depth of hooked foot	160
Max. clamping spread (external pulling)	160

Standards