

Fabory Jobber drill conical
MK2 DIN 345 RN HSS Black
16,0 MM



Article number	F0129.160.001
Brand	-
UBB	240201031319
UNSPSC	23241639
EAN	8715494648547
PKG. of 1	Full Box Only

Technical Parameters

Total length	218
Diameter drill	16
Holding system	Conical plug-in axle
Cutting length	130
Suitable for steel	Yes
Cutting material	HSS
Tip angle	118
Shank shape	Morse taper
Cutting direction	Right
Spiral drill	Yes

Standards