



Studbolt with 2 heavy hexagon nuts ASTM A193/A194 Steel Plain Gr.B7 - Gr.2H 1.7/8X735 (29)

| | |
|----------------|---------------|
| Article number | PIMI0476735 |
| Brand | - |
| UBB | 500635810814 |
| UNSPSC | 00000000 |
| EAN | |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|-------------------|---------------|
| Diameter | 1.7/8 Inch |
| Length | 735 mm |
| Class | Gr.B7 - Gr.2H |
| Material | Steel |
| Surface treatment | Plain |

| | |
|------|---|
| Info | Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. |
|------|---|

Standards

| | |
|------|-----------|
| ASTM | A193/A194 |
|------|-----------|

Technical Specification

| | |
|--------|-----|
| L (mm) | 735 |
|--------|-----|

Technical Drawing

FABORY

