



## Studbolt with 2 heavy hexagon nuts ASTM A193/A194 Steel Zinc plated Gr.B7 - Gr.2H 3/4X390 (15.3/8)

Article number PIMI1191390

Brand -

UBB

UNSPSC

EAN

PKG. of 1 Full Box Only

### Technical Parameters

Diameter	3/4 Inch
Length	390 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Surface treatment	Zinc plated

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

### Standards

ASTM A193/A194

### Technical Specification

L (mm)	390
--------	-----

### Technical Drawing

# FABORY

