



**Studbolt with 2 heavy
hexagon nuts ASTM A193/
A194 Steel Zinc plated
Gr.B7 - Gr.2H 2 Inch X1100
(43.5/16)**

| | |
|----------------|---------------|
| Article number | PIMI1509100 |
| Brand | - |
| UBB | |
| UNSPSC | |
| EAN | |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|-------------------|---------------|
| Diameter | 2 Inch |
| Length | 1100 mm |
| Class | Gr.B7 - Gr.2H |
| Material | Steel |
| Surface treatment | Zinc plated |

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

| | |
|------|-----------|
| ASTM | A193/A194 |
|------|-----------|

Technical Specification

| | |
|--------|------|
| L (mm) | 1100 |
|--------|------|

Technical Drawing

FABORY

