



Studbolt with 2 heavy hexagon nuts ASTM A193/ A194 Steel Zinc plated yellow passivated Gr.B7 - Gr.2H 1.1/8X235 (9.1/4)

Article number	PIMI2285235
Brand	-
UBB	500641446249
UNSPSC	00000000
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1.1/8 Inch
Length	235 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Surface treatment	Zinc plated yellow passivated

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194
------	-----------

Technical Specification

L (mm)	235
--------	-----

Technical Drawing

FABORY

