



Studbolt with 2 heavy hexagon nuts ASTM A193/ A194 Steel Zinc plated yellow passivated Gr.B7 - Gr.2H 1.1/8X280 (11)

| | |
|----------------|---------------|
| Article number | PIMI2285280 |
| Brand | - |
| UBB | |
| UNSPSC | |
| EAN | |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|-------------------|-------------------------------|
| Diameter | 1.1/8 Inch |
| Length | 280 mm |
| Class | Gr.B7 - Gr.2H |
| Material | Steel |
| Surface treatment | Zinc plated yellow passivated |

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

| | |
|------|-----------|
| ASTM | A193/A194 |
|------|-----------|

Technical Specification

| | |
|--------|-----|
| L (mm) | 280 |
|--------|-----|

Technical Drawing

FABORY

