



**Studbolt with 2 heavy
hexagon nuts ASTM
A193/A194 Steel Hot dip
galvanized Gr.B7 - Gr.2H
5/8X90 (3.1/2)**

Article number	PIMI4158090
Brand	-
UBB	500627542755
UNSPSC	00000000
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	5/8 Inch
Length	90 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Surface treatment	Hot dip galvanized

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194
------	-----------

Technical Specification

L (mm)	90
--------	----

Technical Drawing

FABORY

