



**Studbolt with 2 heavy hexagon nuts ASTM A193/A194 Steel Plain Gr.B7M - Gr.2HM 2.1/4X515 (20.1/4)**

Article number	PIMJ0571515
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

**Technical Parameters**

Diameter	2.1/4 Inch
Length	515 mm
Class	Gr.B7M - Gr.2HM
Material	Steel
Surface treatment	Plain

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	---

**Standards**

ASTM	A193/A194
------	-----------

**Technical Specification**

L (mm)	515
--------	-----

**Technical Drawing**

# FABORY

