



**Studbolt with 2 heavy  
hexagon nuts ASTM A193/  
A194 Stainless steel Plain  
Gr.B8M Cl.2 - Gr.8M 1 Inch  
X155 (6.1/8)**

Article number	PIMPF254155
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

**Technical Parameters**

Diameter	1 Inch
Length	155 mm
Class	Gr.B8M Cl.2 - Gr.8M
Material	Stainless steel
Surface treatment	Plain

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	---

**Standards**

ASTM	A193/A194
------	-----------

**Technical Specification**

L (mm)	155
--------	-----

**Technical Drawing**

FABORY

