



**Studbolt with 2 heavy
hexagon nuts ASTM A320/
A194 Stainless steel Plain
Gr.B8M Cl.2 - Gr.8M 5/8X100
(4)**

| | |
|----------------|---------------|
| Article number | PIMPR158100 |
| Brand | - |
| UBB | |
| UNSPSC | |
| EAN | |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|-------------------|---------------------|
| Diameter | 5/8 Inch |
| Length | 100 mm |
| Class | Gr.B8M Cl.2 - Gr.8M |
| Material | Stainless steel |
| Surface treatment | Plain |

| | |
|------|---|
| Info | Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. |
|------|---|

Standards

| | |
|------|-----------|
| ASTM | A320/A194 |
|------|-----------|

Technical Specification

| | |
|--------|-----|
| L (mm) | 100 |
|--------|-----|

Technical Drawing

FABORY

