



Studbolt with 2 heavy hexagon nuts ASME SA193/SA194 Steel Plain Gr.B7 - Gr.2H 5/8X125 (5)

Article number	PIMT0158125
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	5/8 Inch
Length	125 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Surface treatment	Plain

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	---

Standards

ASME	SA193/SA194
------	-------------

Technical Specification

L (mm)	125
--------	-----

Technical Drawing

FABORY

