



Studbolt with 2 heavy hexagon nuts ASME SA193/SA194 Steel Plain Gr.B7 - Gr.2H 1.1/4X360 (14.1/4)

| | |
|----------------|---------------|
| Article number | PIMT0317360 |
| Brand | - |
| UBB | |
| UNSPSC | |
| EAN | |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|-------------------|---------------|
| Diameter | 1.1/4 Inch |
| Length | 360 mm |
| Class | Gr.B7 - Gr.2H |
| Material | Steel |
| Surface treatment | Plain |

| | |
|------|---|
| Info | Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. |
|------|---|

Standards

| | |
|------|-------------|
| ASME | SA193/SA194 |
|------|-------------|

Technical Specification

| | |
|--------|-----|
| L (mm) | 360 |
|--------|-----|

Technical Drawing

FABORY

