

Hexagon socket countersunk head screw UNC ASME B18.3 Alloy steel ASTM F835 Zinc plated 3/8-16X1/2 ft



Article number	U07415.037.0050
Brand	-
UBB	500621039295
UNSPSC	31161518
EAN	8717077368507
PKG. of 50	Full Box Only

Technical Parameters

Diameter	3/8 Inch
Length	1/2 Inch
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Alloy steel
Material technical	ASTM F835
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse

Standards

ASME	B18.3
------	-------

Info ft = fully threaded All dimensions in above table are in inches. Marking of these screws is not mandatory. Due to the unfavourable head geometry these fasteners have reduced loadability. Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can

cause thread fit problems.

FABORY

Technical Specification

A	0.781
H	0.234
J	0.21875
LT (min.)	1.25
Threads per inch	16

Technical Drawing

