



**Hexagon socket  
countersunk head screw  
UNF ASME B18.3 Alloy steel  
ASTM F835 Plain #10-32X2  
Inch**

Article number	U07566.019.0200
Brand	-
UBB	500621046381
UNSPSC	31161518
EAN	8717077369146
PKG. of 1	Full Box Only

**Technical Parameters**

Diameter	NO.10
Length	2 Inch
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Alloy steel
Material technical	ASTM F835
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Fine

Info

ft = fully threadedAll dimensions in above table are in inches.Marking of these screws is not mandatory.Due to the unfavourable head geometry these fasteners have reduced loadability.Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can

**Standards**

ASME	B18.3
------	-------

**FABORY** cause thread fit problems.

**Technical Specification**

A	0.411
H	0.127
J	0.125
LT (min.)	0.88
Threads per inch	32

**Technical Drawing**

