



**Hexagon socket
countersunk head screw
UNF ASME B18.3 Alloy steel
ASTM F835 Zinc plated
5/16-24X1.1/2**

Article number	U07567.031.0150
Brand	-
UBB	500625368708
UNSPSC	31162400
EAN	8715492887665
PKG. of 50	Full Box Only

Technical Parameters

Diameter	5/16 Inch
Length	1.1/2 Inch
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Alloy steel
Material technical	ASTM F835
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Fine

Info

All dimensions in above table are in inches. Marking of these screws is not mandatory. Due to the unfavourable head geometry these fasteners have reduced loadability. Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can cause thread fit problems.

Standards

ASME	B18.3
------	-------

Technical Specification

A	0.656
H	0.198
J	0.1875
LT (min.)	1.12
Threads per inch	24

Technical Drawing

