



**Machine screw round head
slot UNC asme B18.6.3
ASME B18.6.3 Low carbon
steel Zinc plated #8-32X4
Inch**

| | |
|----------------|-----------------|
| Article number | U24210.016.0400 |
| Brand | - |
| UBB | 500624908702 |
| UNSPSC | 31161504 |
| EAN | 8717077799240 |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|-------------------|----------------------------|
| Diameter | NO.8 |
| Length | 4 Inch |
| Driving features | Slotted |
| Head shape | Round head |
| Material | Low carbon steel |
| Thread direction | Right |
| Surface treatment | Zinc plated |
| Thread | Unified National Coarse |
| Threads per inch | 32 |

| | |
|------|---|
| Info | Screws with diameter ≤ No.5 and length ≤ 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min.Screws with diameter No.5 and length ≤ 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min. |
|------|---|

Standards

| | |
|------|---------|
| ASME | B18.6.3 |
|------|---------|

Technical Specification

| | |
|----------|-------|
| A (max.) | 0.309 |
|----------|-------|

Technical Drawing

| | |
|----------|-------|
| H (max.) | 0.12 |
| J (max.) | 0.054 |
| T (max.) | 0.077 |

