



Hexagon socket countersunk head screw UNC ASME B18.3 Stainless steel ASTM F879 304 CW / CW1 3/4-10X1.3/4 ft

Article number	U51060.075.0175
Brand	-
UBB	500621322253
UNSPSC	31161518
EAN	8717077392526
PKG. of 5	Full Box Only

Technical Parameters

Diameter	3/4 Inch
Length	1.3/4 Inch
Class	CW / CW1
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Stainless steel
Material technical	ASTM F879 304
Thread direction	Right
Thread	Unified National Coarse

Standards

ASME	B18.3
------	-------

Info

ft = fully threaded
All dimensions in above table are in inches. Marking of these screws is not mandatory. Due to the unfavourable head geometry these fasteners have reduced loadability. Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can

FABORY cause thread fit problems.

Technical Specification

A	1.438
H	0.396
J	0.5
LT (min.)	2
Threads per inch	10

Technical Drawing

