



Machine screw binding head slot UNC asme B18.6.3 ASME B18.6.3 Stainless steel A2 (AISI 304/18-8) #4-40X1/4

Article number	U51140.011.0025
Brand	-
UBB	500625012546
UNSPSC	31161504
EAN	8717077791916
PKG. of 100	Full Box Only

Technical Parameters

Diameter	NO.4
Length	1/4 Inch
Driving features	Slotted
Head shape	Binding head
Material	Stainless steel
Material technical	ASTM F837 304
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	40

Info
Screws with diameter \leq No.5 and length \leq 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length \leq 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

Standards

ASME B18.6.3

Technical Specification

O (max.) 0.068

Technical Drawing

F (max.) 0.025

A (max.) 0.235

J (max.) 0.039

T (max.) 0.042

