



Machine screw round head slot UNC asme B18.6.3 ASME B18.6.3 Stainless steel A2 (AISI 304/18-8) #8-32X1.1/2

Article number	U51213.016.0150
Brand	-
UBB	500625024848
UNSPSC	31161504
EAN	8717077797819
PKG. of 1	Full Box Only

Technical Parameters

Diameter	NO.8
Length	1.1/2 Inch
Driving features	Slotted
Head shape	Round head
Material	Stainless steel
Material technical	ASTM F837 304
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	32

Info

Screws with diameter \leq No.5 and length \leq 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length \leq 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

Standards

ASME	B18.6.3
------	---------

Technical Specification

A (max.)	0.309
----------	-------

Technical Drawing

H (max.)	0.12
J (max.)	0.054
T (max.)	0.077

