



**Machine screw round head  
slot UNC asme B18.6.3  
ASME B18.6.3 Stainless  
steel A2 (AISI 304/18-8)  
#8-32X3 Inch**

Article number	U51213.016.0300
Brand	-
UBB	500625025266
UNSPSC	31161504
EAN	8717077797857
PKG. of 1	Full Box Only

**Technical Parameters**

Diameter	NO.8
Length	3 Inch
Driving features	Slotted
Head shape	Round head
Material	Stainless steel
Material technical	ASTM F837 304
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	32

Info	Screws with diameter ≤ No.5 and length ≤ 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min.Screws with diameter No.5 and length ≤ 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.
------	---

**Standards**

ASME	B18.6.3
------	---------

**Technical Specification**

A (max.)	0.309
----------	-------

**Technical Drawing**

H (max.)	0.12
J (max.)	0.054
T (max.)	0.077

