



**Machine screw flat
countersunk UNC asme
B18.6.3 ASME B18.6.3
Stainless steel A2 (AISI
304/18-8) 3/8-16X1.1/2**

Article number	U51300.037.0150
Brand	-
UBB	500625045140
UNSPSC	31161504
EAN	8715492971562
PKG. of 25	Full Box Only

Technical Parameters

Diameter	3/8 Inch
Length	1.1/2 Inch
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	ASTM F837 304
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	16

Info	Screws with diameter ≤ No.5 and length ≤ 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min.Screws with diameter No.5 and length ≤ 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.
------	---

Standards

ASME	B18.6.3
------	---------

Technical Specification

A (max.)	0.717
----------	-------

Technical Drawing

H (max.) 0.23

No. cross recess 4

