



Machine screw fillister head slot UNC asme B18.6.3 ASME B18.6.3 Stainless steel A2 (AISI 304/18-8) 1/4-20X5/8

Article number	U51341.025.0062
Brand	-
UBB	500625055297
UNSPSC	31161504
EAN	8717077791749
PKG. of 50	Full Box Only

Technical Parameters

Diameter	1/4 Inch
Length	5/8 Inch
Driving features	Slotted
Head shape	Fillister head
Material	Stainless steel
Material technical	ASTM F837 304
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	20

Info
Screws with diameter \leq No.5 and length \leq 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length \leq 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

Standards

ASME B18.6.3

Technical Specification

O (max.) 0.237

Technical Drawing

A (max.) 0.414

H (max.) 0.17

J (max.) 0.075

T (max.) 0.109

