FABORY



KIPP Indexing plungers with threaded pin, with locknut Metrický jemný závit Nerezová ocel 1.4305, netvrzený kolik 4MM

Objednací číslo	58593.000.004
Značka	-
UBB	500689874575
UNSPSC	31162807
EAN	4059245014156
BAL. od 3	Pouze celé balení

Technické parametry

D1_MM	8mm
Materiál	Nerezocel
Technický materiál	1.4305
Závit	Metrický jemný závit
Info	Material: Stainless steel. Threaded sleeve 1.4305. Indexing pin 1.4305.Version: Indexing pin not hardened, ground and bright.Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been disengaged. Special grips can be fitted on the projecting threaded pin. This pin is also suitable for automatic actuation e.g. program controlled

Standardy

	pneumatic cylinder or by remote control using Bowden cables.

Technická specifikace

D	4
D1	8
D2	3
F1 = springiness beginning in N	6
F2 = springiness end in N	12
F x 30°	1
H	4
L1	15
L2	6
L3	7
L4	13
L	32
P	1
SW1	10
SW2	13

Technický nákres

