FABORY



KIPP Ball lock pins, self-locking Nerezová ocel 16X70MM

Objednací číslo	58650.160.070
Značka	-
UBB	500689919396
UNSPSC	31162807
EAN	4059245023363
BAL. od 1	Pouze celé balení

Technické parametry

D1_MM	16mm
Materiál	Nerezocel
Info	Material: Metal parts stainless steel.Version: Bright.Note: Ball lock pins are used for quick and easy fastening and joining of parts and work pieces. The two balls are disengaged by pressing the push button and the pin can be slipped into holes in the work pieces. Release the button to lock the balls and secure the connection. Corrosion resistant. Option for connecting retaining cable. Application temperature max. +250 °C. Shearing force double shear (F) = S · τ aB max.Accessories: Safety spiral cable

Standardy

	K0367. Retaining cable with loop K0367. Key ring K0367.Bushing for ball lock pins K0724.

Technická specifikace

Receiving hole (H11)	16
D	33
D1	16
D2	19
D3	20
L1	13.3
L2	34.6
L	70
Střižná síla (dvojitý střih), max. (kN)	153

Technický nákres

