FABORY



10X350

Objednací číslo	95718FIS
Značka	-
UBB	500616793740
UNSPSC	31161601
EAN	4006209957189
BAL. od 10	Pouze celé balení

Technické parametry

ETA-Certifikát	Yes
Info	The allowable load is valid for one single anchor, at non-cracked concrete (pressure zone) with concrete class C20/25, in combination with bolt class 5.8 and if the Scr, N and Ccr, N are taken in to account. When reduction on spacing and edge distance take place a re-calculation of forces should be carried out.For a complete chemical fixing, the resin capsule and internal threaded anchor have to be ordered separately. Setting tool is enclosed in each packing.

Standardy

Technická specifikace

Technický nákres

FABORY

