
FABORY



# Strukturbausatz, CE EN 15048 Stahl Elektrolytisch verzinkt 8.8/8 M12X300

| | |
|---|---|
| Artikelnummer | 01222.120.300 |
| Marke | - |
| UBB | 500613345171 |
| UNSPSC | 31161620 |
| EAN | 8715494441452 |
| PKG. von 25 | Nur komplette Verpackung |

## Technische Parameter

| | |
|---|---|
| Klasse | 8.8/8 |
| Antriebsart | Hexagon |
| Kopfform | Sechskantkopf |
| Material | Stahl |
| Gewinderichtung | Rechts |
| Oberfläche | Elektrolytisch verzinkt |
| Gewinde | Metrisches Gewinde |
| Info | Full boxes only.European constructions must comply with the Construction Products Regulation (CPR) in order to ensure the safety of persons and objects.Generally, construction products according to harmonized European standards (hEN standards) should be used for this purpose. Bolting assemblies for non-preloaded structural bolting according to EN 15048-1 are |

## Standards

| | |
|---|---|
| EN | 15048 |
| ISO | 4014/4032 |

compliant with the CPR.Compared to 'common' bolts ISO 4014/4017 (previously DIN 931/933) and nuts ISO 4032 (DIN 934), bolts and nuts according to EN 15048 are additionally marked with 'SB' (Structural Bolting), and the packaging is provided with the CE-mark.The manufacturer of the assemblies is CE certified for their production.Bolts and nuts are packaged together in single sealed boxes.A Declaration of Performance (DoP) is available.

## Technische Spezifikation

## Technische Zeichnung

