
FABORY



Structural assembly set ISO metric thread EN 15048 Stahl Feuerverzinkt 8.8/8 M12X80

Artikelnummer	01405.120.080
Marke	-
UBB	500574458971
UNSPSC	31161620
EAN	8715494283779
PKG. von 50	Nur komplette Verpackung

Technische Parameter

Durchmesser	M12
Länge	80 mm
Klasse	8.8/8
Antriebsart	Hexagon
Kopfform	Sechskantkopf
Material	Stahl
Gewinderichtung	Rechts
Oberfläche	Feuerverzinkt
Gewinde	Metrisches Gewinde
Info	Full boxes only.European constructions must comply with the Construction Products Regulation (CPR) in order to ensure the safety of persons and objects.Generally, construction products according to harmonized European standards (hEN standards) should be used for this purpose. Bolting assemblies for non-preloaded structural

Standards

EN	15048
ISO	4014/4032

bolting according to EN 15048-1 are compliant with the CPR.Compared to 'common' bolts ISO 4014/4017 (previously DIN 931/933) and nuts ISO 4032 (DIN 934), bolts and nuts according to EN 15048 are additionally marked with 'SB' (Structural Bolting), and the packaging is provided with the CE-mark.The manufacturer of the assemblies is CE certified for their production.Bolts and nuts are packaged together in single sealed boxes.A Declaration of Performance (DoP) is available.ISO metrisch

Technische Spezifikation

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	80
m (max.)	10.8
P	1.75
s	18

Technische Zeichnung

