
FABORY



Assembly set for pressure vessels ISO 4014/4032 Stahl Feuerverzinkt 5.6/5.2 M12X55

Artikelnummer	08753.120.055
Marke	-
UBB	500650920795
UNSPSC	31161620
EAN	8717077306547
PKG. von 100	Nur komplette Verpackung

Technische Parameter

Durchmesser	M12
Länge	55 mm
Klasse	5.6/5.2
Antriebsart	Hexagon
Kopfform	Sechskantkopf
Material	Stahl
Gewinderichtung	Rechts
Oberfläche	Feuerverzinkt
Gewinde	Metrisches Gewinde
Info	Specific features of fasteners for pressure vessels:Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from –10°C up to +300°C.Meets the requirements of AD2000-W7, TRD106 and DIN 267-13Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a

Standards

ISO	4014/4032

certificate EN 10204 3.1 by marking the fasteners with the property class and the manufacturer’s mark. This recognition is equally accepted by Lloyd's Register Energy.

Technische Spezifikation

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	55
m (max.)	10.8
P	1.75
s	18

Technische Zeichnung

