
FABORY



Assembly set for pressure vessels ISO 4014/4032 Stahl Feuerverzinkt 5.6/5.2 M16X75

Artikelnummer	08753.160.075
Marke	-
UBB	500650921454
UNSPSC	31161620
EAN	8717077306615
PKG. von 25	Nur komplette Verpackung

Technische Parameter

Durchmesser	M16
Länge	75 mm
Klasse	5.6/5.2
Antriebsart	Hexagon
Kopfform	Sechskantkopf
Material	Stahl
Gewinderichtung	Rechts
Oberfläche	Feuerverzinkt
Gewinde	Metrisches Gewinde
Info	Specific features of fasteners for pressure vessels:Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from –10°C up to +300°C.Meets the requirements of AD2000-W7, TRD106 and DIN 267-13Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a

Standards

ISO	4014/4032

certificate EN 10204 3.1 by marking the fasteners with the property class and the manufacturer’s mark. This recognition is equally accepted by Lloyd's Register Energy.

Technische Spezifikation

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	75
m (max.)	14.8
P	2
s	24

Technische Zeichnung

