FABORY

Hexagon head bolt ISO 4014 Steel Zinc plated yellow passivated 10.9 M8X70

Article number	04104.080.070
Brand	-
UBB	954351987837
UNSPSC	31161620
EAN	8715493175181
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M8
Length	70 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

NF	E25-112
DIN	931
NEN	1555
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	70
P	1.25
s	13

Technical Drawing

