FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M7X40

Article number	01000.070.040
Brand	-
UBB	950351003385
UNSPSC	31161620
EAN	8715492007285
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M7
Length	40 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
NF	E25-112
ASME	B18.2.3.1M
ISO	4014
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	26
b (min.): L≤125mm	20
d-D	M7
k	4.8
L (mm)	40
P	1
s	11

Technical Drawing

