FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M8X60

Article number	01000.080.060
Brand	-
UBB	950351004110
UNSPSC	31161620
EAN	8715492007414
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	60 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
ISO	4014
NF	E25-112
NEN	1555
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	60
P	1.25
s	13

Technical Drawing

