FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M8X130

Article number	01000.080.130
Brand	-
UBB	950351005026
UNSPSC	31161620
EAN	8715492007537
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	130 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
ASME	B18.2.3.1M
NF	E25-112
DIN	931
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	130
P	1.25
s	13

Technical Drawing

